## room-temperature, low-noise

## AMPLIFIED MCT DETECTOR

## **Specifications**

Daylight Solutions is pleased to provide a fully integrated receiver with detector, low-noise amplifier, and temperature control, all in one compact package. Now you can get 245 °K performance with no external cooling.



- 2 stage TEC cooled detector to 245 °K
- Room Temperature Operation
- Wide Field of View, 78 degrees
- Photoconductive configuration

Detector Material: HgCdTe
Spectral Response: 4–12 μm

**D\*:** >2.5 E<sup>+9</sup> cm Hz $\frac{1}{2}$ /W

Active Detector Area: 1 mm × 1 mm

Fast Response: <3 ns rise time

RF Output: SMA connector

Responsivity: >2,500 V/W

Power Supplies: +15VDC, +5VDC

**Power Consumption:** < 3 Watts

**Dimensions:** 3.0" × 1.75" × 1.90"

Call today for updated pricing and availability.

I 5378 Avenue of Science, Suite 200 San Diego, CA 92128 Phone: 858.432.7500 Fax: 858.432-5737

Email: info@daylightsolutions.net www.daylightsolutions.com



